USB 2.0 A Male to Female Cable

pro-signal




RoHS Compliant

Specifications

Connector to Connector : Type A Plug to Type A Receptacle

USB Standard : USB 2.0 Jacket Colour : Grey

Diagram



Notes:

- 1. Materials
- 1.1 Cable: 7/0.12BCx1P+7/0.20BCx2C+AM+D(7/0.12BC)+B(16/3/0.12ALM)+Grey PVC Jacket. OD=Ø4.5±0.15mm.

Cable Marking: USB 2.0 Cable Fully Rated 30V 80°C

- 1.2 Connector P1: USB A Type Male: Solder Type, Gold Flash Contacts, Nickel Plated Shell. Connector P2: USB A Type Female: Solder Type, Gold Flash Contacts, Nickel Plated Shell.
- 1.3 All Hood: Molded Grey PVC.

Part Number Table

Description	Length ("L")	Part Number
USB 2.0 A Male to Female Cable, Grey	250 ±30mm	PSG91432
	500 ±30mm	PSG91433
	1000 ±30mm	PSG91434
	2000 ±50mm	PSG91435
	3000 ±70mm	PSG91436
	5000 ±70mm	PSG91437

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

