



- Easily applied to bolts or studs with a light hammer blow or turning of the mount.
- Designed for use with cable ties to route and secure cable bundles, air, water and hydraulic lines.

Part Number: TMSTHS19-C0  
Product Family: Stud Tie Mounts  
Product Line: Stud Mounts

RoHS Compliancy Status: Compliant

Part Description: Cable Tie Mounts for Threaded Studs

Product Type: Cable Tie Mounts - Stud Mounted

Material: Impact Modified Weather Resistant Nylon 6.6

Color: Black

Height (In.): 1.10

Height (mm): 27.9

Length (In.): 1.99

Length (mm): 50.6

Width (In.): 1.00

Width (mm): 25.4

Environment: Outdoors

Flammability Rating: UL94 V-2

Metric Screw Size: M19

Mounting Method: 3/4" Stud Dia. (19mm)

Screw Size: 3/4 (M19)

Std. Pkg. UOM: PK

Used With Cable Ties: M, I, S, HS, LH, H

