



Secures stacked cables folds and breakouts plus laminated and molded bus bars.
Mounting Application: Use one (1) base, one (1) corresponding size plate, and one (1) Intermediate cross section cable tie.

Part Number:	FCBI2-S10-C20
Product Family:	Flat Cable Mounting System - FCB Base
Product Line:	Flat/Ribbon Cable
RoHS Compliancy Status:	Compliant
Part Description:	Flat Cable Mounting Base
Product Type:	Cable Tie Mounts - Flat Cable Mounting System
Material:	Nylon 6.6
Color:	Black
UL Recognized:	E136577
Height (In.):	.15
Height (mm):	3.8
Length (In.):	3.50

Length (mm):	88.9
Width (In.):	.38
Width (mm):	9.5
Environment:	Indoors
Hole Diameter (In.):	.20
Hole Diameter (mm):	5.1
Max. Flat Cable Width (In.):	2.00
Max. Flat Cable Width (mm):	50.8
Metric Screw Size:	M5
Mounting Method:	#10 (M5) Screw
Screw Size:	#10 (M5)
Std. Pkg. UOM:	PK
Used With Cable Ties:	I
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100