



Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

Part Number:	FCM2-S6-C14
Product Family:	Latching Flat Cable Mounts
Product Line:	Flat/Ribbon Cable
RoHS Compliancy Status:	Compliant
Part Description:	Adhesive Backed Latching Flat Cable Holder
Product Type:	Mounting Device
Material:	Nylon 6.6
Color:	Gray
UL Recognized:	E136577
Length (In.):	5.06
Length (mm):	128.5
Width (In.):	1.00
Width (mm):	25.4

Cable Width (In.):	2.22
Cable Width (mm):	56.4
Environment:	Indoors
Flammability Rating:	UL94 V-2
Max. Flat Cable Width (In.):	2.00
Max. Flat Cable Width (mm):	50.8
Metric Screw Size:	M3
Mounting Method:	#6 (M3) Screw
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100