


Part Number: P-S11S21-M4RX

Voltage Test Station with Mult-Environment Flashing Voltage Indicator and Safe-Test Point, Horizontal Mount, UL Type 12 Housing

<https://shop.graceport.com/products/p-s11s21-m4rx>



Product Specifications

Component Details	
Part Number	P-S11S21-M4RX
Includes	Voltage Indicator (R-3W2) and Safe-Test Point (R-3MT), UL Type 12 Housing, Horizontal Mount
Electrical Specifications	
Operational Temperature Range	-20°C to +55°C
Storage Temperature Range	-45°C to + 85°C
Operational Range AC Single/3-Phase	40-600VAC 50/60/400Hz
Operational Range DC or Stored Energy	30-600 VDC
Mechanical Specifications	
Enclosure Rating	IP65
Housing Size	M Size Housing
UL Type	Type 12
Latch	Type 304 Stainless Steel
Cover	Polycarbonate, UV rated
Mount	Horizontal

Geometric Data

Width	6.50 in
Height	3.78 in
Depth	1.60 in

Commercial Data

Country of Origin	US
Schedule B Code	8531.20.00400

Approval Certifications

Logo	Approval	Additional Text	Certificate Name	
	UL Underwriters Laboratories Inc.	Outlets UL Recognized for 15A	E207344	
RoHS	RoHS Restriction of Hazardous Substances		SS0002-0616-B-RH	
	CE European Conformity	INGR0516-A-00	SS0002-0616-A-CE	

CAD Files

File Format	
2D PDF File	

Datasheets

Name	
Voltage Test Station Datasheet	
Voltage Test Station Installation Guide	
Voltage Test Station Single Phase Wiring Diagram	
Voltage Test Station Single Phase Wiring Diagram	



Don't see what you're looking for?

Contact us at sales@gracetechnologies.com, call 1-800-280-9517 or visit www.graceport.com to chat with our customer service.