



G10 Comfort Plus™ Blue Nitrile Gloves

STRENGTH AND COMFORT COMBINED

There's no need to choose between protection and productivity with KleenGuard® G10 Comfort Plus™ Gloves. An advanced formulation delivers superior strength and tactile sensitivity.

- Ideal for light-duty tasks
- Enables workers to feel the shape and texture of objects
- Helps promote more accurate work and overall durability

KleenGuard® Hand Protection is designed with human-centric engineering that enables rather than inhibits – allowing for maximum productivity and safety.

**KleenGuard® Hand Protection –
Perform with Distinction.**





G10

COMFORT PLUS™ BLUE NITRILE GLOVES

- ▶ Helps minimize contamination risk
- ▶ Supports increased speed and accuracy
- ▶ Recycle after use

FEATURES:

- 0.10 mm (4 mil) thickness
- Powder-free and ambidextrous
- Not made with rubber latex

TYPICAL USES:

- Light-duty manufacturing
- Transportation and distribution
- General maintenance
- Electrical assembly
- Painting
- Food processing
- Food service

0.10 mm (4 mil) finger thickness
for excellent tactile
sensitivity

Textured fingertips for
better grip and control

AQL 2.5
(Acceptable Quality Limit
levels defined according
to ISO 2859-1)

Beaded cuff to
make donning
easier and prevent
roll down



G10 | COMFORT PLUS™ BLUE NITRILE GLOVES

| | XS (6) | S (7) | M (8) | L (9) | XL (10) | Case Count |
|---------------|--------|-------|-------|-------|---------|--------------------------------|
| Comfort Plus™ | 54185 | 54186 | 54187 | 54188 | 54189 | 100 gloves/box • 10 boxes/case |

Visit our website at
www.kcprofessional.co.uk
OR contact us at
0800 917 9908

