5 Pin 180 Degree Midi DIN Plug to Plug Lead





Features


- 5-Pin DIN plug to 5-Pin DIN plug MIDI lead
- · Metal connectors with rubber strain reliefs
- · PVC insulated, shielded cable

Specifications

Connector Type A : IEC 60130-9, DIN Plug, 180°, 5 Way Connector Type B : IEC 60130-9, DIN Plug, 180°, 5 Way

Jacket Colour : Black

Diagram



Part Number Table

Description	Length	Part Number
5 Pin 180 Degree Midi DIN Plug to Plug Lead	1m	PLS00594
	2m	PLS00595
	3m	PLS00596
	6m	PLS00597
	10m	PLS00598

Dimensions : Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. PULSE is the registered trademark of Premier Farnell Limited 2019.

Page <1>

Newark.com/b/Pulse Farnell.com/b/Pulse sg.element14.com/b/pulse

