



The clips hold wire bundles securely. Clips are placed on the bundle then attached to the panel. Designed for pre-drilled holes.

Part Number:	SICH75-C
Product Family:	Snap-In Clips
Product Line:	Push/Tree Barb
RoHS Compliancy Status:	Compliant
Part Description:	Snap-In Wire Clip
Product Type:	Mounting Device
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Height (In.):	.96
Height (mm):	35.6
Environment:	Indoors
Flammability Rating:	UL94 V-2

Max. Bundle Diameter (In.): .75

Max. Bundle Diameter (mm): 19.1

Max. Panel Thickness (In.): .10

Max. Panel Thickness (mm): 2.5

Mounting Method: Push Barb

Panel Hole Diameter (In.): .250

Panel Hole Diameter (mm): 6.4

Std. Pkg. UOM: PK

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100