

4W LED Candle Filament Bulb

pro-ELEC



Specifications

Lamp Style	: Filament Candle
LED Colour	: Warm White
Colour Temperature	: 2700K
Dimmable	: Not Dimmable
Beam Angle	: 360 Degree
Equivalent Wattage	: 40W
Luminous Flux	: 470lm
Power Rating	: 4W
Supply Voltage	: 230V, 50Hz
Energy Rating	: A++
Colour Rendering	: ≥ 80
External Diameter	: 35mm
Life	: 25000 hrs.

Part Number Table

Description	External Length	Part Number
Lamp Led Candle Filament 4W 2700K E14	98mm	PEL00905
Lamp Led Candle Filament 4W 2700K B22	90mm	PEL00906

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-ELEC