

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731140392

Status:


Active

Overview:

FCT D-Sub Connectors

Description:

FCT Plastic Backshell with Female D-Sub Connector, Shielded, Shell Size 3, Straight Cable Outlet, IP67 Waterproof, Large Inner Chamber, with Locking Screws



Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General	
Product Family	D-Sub Products
Series	173114
IP Rating	IP67
Overview	FCT D-Sub Connectors
Product Category	Backshell
Product Name	FCT Products
Type	Plastic
UPC	191130516742
Physical	
Cable Diameter	8.00-10.50mm
Material - Backshell	PC+ABS
Material - Screw	Brass
Material - Seal	Elastomer
Mounting Style	Locking Screw
Net Weight	35.000/g
Orientation	Straight
Packaging Type	Bag
Plating - Backshell	Nickel
Shield Type	Shielded Plastic
Shielded	Yes
Temperature Range - Operating	-25° to +70°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Material Info	
Engineering Number	FWH3A-25S-3649

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

173114 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION