



For retaining wires, cable, components or tubing away from panel or conductive chassis. Finger grip flanges can be easily locked or unlocked for revisions. Hand installed in pre-drilled hole.

Part Number:	WS50-50-C
Product Family:	Wire Standoffs
Product Line:	Push/Tree Barb

RoHS Compliancy Status:	Compliant
-------------------------	-----------

Part Description:	Push Barb Wire Standoff Clip
-------------------	------------------------------

Product Type:	Mounting Device
---------------	-----------------

Material:	Nylon 6.6
-----------	-----------

Color:	Natural
--------	---------

UL Recognized:	E136577
----------------	---------

Environment:	Indoors
--------------	---------

Flammability Rating:	UL94 V-2
----------------------	----------

Max. Bundle Diameter (In.):	.47
-----------------------------	-----

Max. Bundle Diameter (mm):	11.9
Max. Panel Hole Diameter Range (In.):	.19 - .20
Max. Panel Hole Diameter Range (mm):	4.7 - 4.9
Max. Panel Thickness (In.):	.08
Max. Panel Thickness (mm):	2.0
Mounting Method:	Push Barb
Panel Hole Diameter (In.):	.187
Panel Hole Diameter (mm):	4.7
Standoff Height (In.):	.50
Standoff Height (mm):	12.7
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100