



- Durable nylon cable clamps

Part Number: CCH19-S10-C
Product Family: Fixed Diameter Cable Clamps
Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Heavy Duty Fixed Diameter Cable Clamp

Product Type: Mounting Device

Material: Nylon 6.6

Color: Natural

UL Recognized: E136577

Diameter (In.): .20

Diameter (mm): 5.1

Width (In.): .50

Width (mm): 12.7

Bundle Offset (mm):	10.7
Bundle Offset (In.):	.42
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.20
Hole Diameter (mm):	5.1
Max. Bundle Diameter (In.):	.19
Max. Bundle Diameter (mm):	4.8
Metric Screw Size:	M5
Mounting Method:	#10 (M5) Screw
Screw Size:	#10 (M5)
Std. Pkg. UOM:	PK
Type Of Application:	Heavy Duty
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100