Plastic Enclosure



RoHS Compliant



Features

- · Ideally design for portable, desktop or wall mounted electronic application.
- Space of the recessed area are designed for 4.3", 5.7", 7.0", 8.4" & 10.4" lcd module or touch screen use.
- · Lid & base incorporate a tongue and groove sealing design, optional EPDM gasket can be ordered and installed to meet
- · IP65 rating of waterproof and dust.
- · Put-on rubber feet are included.

Specification

Enclosure Type : Utility Box **Enclosure Material** : ABS External Height - Metric : 30mm External Width - Metric : 100mm : 140mm External Depth - Metric **Body Colour** : White External Height - Imperial : 1.18" External Width - Imperial : 3.94" External Depth - Imperial : 5.51"

Working temperature : -20°C to +80°C.

Part Number Table

Description	Part Number
Plastic Enclosure, Utility Box, ABS, White	MC000909

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

