

SPECIFICATION

Part No. : **AA.105.301621**

Product Name : Titan GPS/GALILEO Antenna AA.105

3M RG174

Fakra Code C Blue SMB(F)

Features : Magnetic Mount

Covert stylish design Wide band input voltage

28db Gain

Gain is Customizable IP-67 Waterproof















1. Introduction

Our AA.105 Titan magnetic mount external antenna is ideal for robust, covert installations where durability and small size is paramount. It is used in telematics and M2M applications, for example in commercial vehicle installations for fleet management. It is fully waterproof to IP67 rating.


2. Specifications

GPS/GALILEO Antenna				
Outline Dimension	25*25*4mm			
Ground Size	25*25*4mm			
Center Frequency	1575.42±3MHz			
Bandwidth	10MHz			
VSWR	1.92 Max			
Axial ratio	3dB Typ.			
Gain @ Zenith	2dBi Typ.			
Impedance	50Ω			
Polarization	RHCP			

	LNA
Frequency	1575.42MHz
Impedance	50Ω
VSWR	1.92 Max.
Gain	30dB Typ.
Gain at Connector*	28.4dB
DC Power Input	2.7~5V
Noise Figure	1.5dB Typ.
Weight	75g
Power Consumption	4.7mA @2.7V 6mA @3.3V 10.3mA @5V
Operating temp	-40°C ~ +85°C
Storage Temp	-40°C ~ +90°C




3. Ceramic Antenna S11 (with housing)






4. Ceramic Antenna Radiation Pattern (with housing)







XZ Plane




YZ Plane



Far-field amplitude of goasial 1583 06-5-8.nsi




Far-field amplitude of goasial 1583 06-5-8.nsi






5. LNA gain






6. LNA S22





7. Drawing




	Name	P/N	Material	Finish	QTY
1	GPS Antenna Housing Top	000111J000015A	PC	Black	1
2	GPS Antenna Housing Bottom	000111J010015A	PC	Black	1
3	Sticker	001011J0700XXA	Matte Silver PET	Silver	1
4	Heat Shrink Tube	001311F0000XXA	PE	Black	1
5	Barcode Label	001011K010017A	PEPA	White	1

	Name	P/N	Spec	Finish	QTY
WW	Connector Type	202311G010003A	FAKRA Code C GEN2	Blue	1
XX	Cable Length		3000±30mm		1
YY	Cable Type	301311F0000XXA	RG174	Black	1



Packaging (Unit: mm)





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.