

BU-P5697-XX

(Test Lead: Male BNC on Each End)



- The BU-P5697 is a coaxial cable test lead with male BNC connectors at each end.
- Material, cable:

Cable	RG-58C/U, complies to Mil-M17/155-00001
Jacket	Non-contaminating PVC
Conductor	20 AWG (19x33) tinned copper
Shield	Tinned copper braid (95% coverage)
- Material, BNC:

Body	Tarnish-resistant nickel-plated brass
Contact	Gold-plated brass
Insulator	PTFE
- Ratings:

Impedance	50 Ohms
Capacitance per foot	30.8 pf
Power loss/100 ft. @ 1 MHz	0.40 dB
Voltage	Hands-free to 500 VRMS
Temperature	-40°C to 85°C
- Length: The "XX" in the model number indicates the length in inches. Standard lengths: 6", 12", 24", 36", 48", 60", 120", 180", 240", 300", and 600"
- RoHS 3 compliant, CE compliant