



WARRANTY  
2 YEARS

The **ANSMANN 16340** 3.6V Li-Ion protected battery (RCR123A) is extremely long lasting and can be recharged up to 2000 times even under tough operating conditions.

- Equivalent to **CR123A** – but rechargeable
- With a very low self-discharge the battery keeps its charge for a long time, even when not used.
- The power to weight ratio is much better than other battery technologies (eg. NiCD/NiMH/PB), with Lithium being much lighter.
- Ideal in modern devices like LED torches, headlights, e-cigarettes, laser pens, etc.
- High capacity of 850 mAh this is perfect for use in high power devices
- Can be used in a wide range of temperatures from -20°C to +60°C.
- The integrated safety board makes this battery slightly larger than the 16340 inside – 17350 (17x35mm approximately)

**INFORMATION**

**Product name:** Protected 16340 Li-Ion  
**Article number:** 1300-0017  
**EAN-Code:** 4013674176922  
**Product:** 17x35x17mm/ 19g  
**Packing + Product:** 86x23x123mm/ 24g  
**Packing unit:** 10 (129x116x131mm) /300g

**Available:** Nov 2021  
**Custom tariff number:** 85076000