





WCFL12 | WIRELESS FLASHLIGHT

- 1200 lumen white LED, 6500K
- Ultra tough nylon, aluminium & TPR construction
- Multi-faceted reflector for long distance beam
- Dual switches for easy mode selection
- Memory switch remembers last mode used
- Press & hold for 2 seconds for Strobe mode
- IP68 dust & water proof 1m submersible
- IK07 super tough shock resistant construction
- 2m drop resistant

BATTERY 3.7v 2600mAh Li-ion

WEIGHT 215g

DIMENSIONS Ø41 x 159mm

- Built-in USB-C charging port with protective cover
- 3 Battery level and charging indicators
- 2A direct USB-C charging fast 4 hours charge time
- 1m USB-C charging cable included
- Can be wirelessly charged with Unilite WCSGL or WCDBL wireless charging pads

(((<mark>/</mark>)))

LUMEN 1200LM | RUNTIME 2-200H | BEAM 251M | IP RATING IP68/IK07

WWW.UNILITE.CO.UK #BUILT TOUGH