





## CRI-1900 | HIGH CRI WORK LIGHT

- 1900 lumen 15.6W high CRI 96+ COB LED
- 4 Colour Temperatures CCT range: 2700K / 3500K / 4500K / 6500K
- Dual power rechargeable and mains
- Memory function remembers last colour setting Mains 15V 1.5A multi-country charger/power lead used
- 2A USB power bank for charging devices
- Super tough nylon polymer construction
- Glow-in-the-Dark strip around reflector

- 210° Rotating stand with magnets & carabiner snap hook
- 180° Rotating handle with tripod hole
- Battery level & charging indicators
- included
- Fast 3 hour charge time

**BATTERY** 7.4v 5000mAh Li-lon

**WEIGHT** 750g

**DIMENSIONS** 188 x 164 x 78mm



LUMEN 1900LM | RUNTIME 1.5-26H | BEAM 48M | IP RATING IP65

WWW.UNILITE.CO.UK #BUILT TOUGH