



CRI-3250 | HIGH CRI WORK LIGHT

- 3250 lumen 30W high CRI 96+ COB LED
- Multiple Colour Temperatures - CCT range: 2700k - 6500k
- Easy twist switch to change colour temperature
- Memory function - remembers last colour used
- Easy twist smooth dimming switch
- Dual power - rechargeable and mains
- 2A USB power bank for charging devices
- Super tough nylon & aluminium construction
- Built-in aluminium heat sinks
- Glow-in-the-Dark strip around reflector for extra visibility
- 170° Rotating stand with 4 strong magnets
- Adjustable head to change light angle
- Battery level & charging indicators
- Mains 15V 1.5A multi-country charger/power lead included

BATTERY 11.1v 5200mAh Li-ion
WEIGHT 1500g
DIMENSIONS 243 x 236 x 125mm



LUMEN 3250LM | RUNTIME 2-64H | BEAM 60M | IP RATING IP65