tesa® Professional 74613 **PRO Duct Tape**

Product Information

Professional Repairing tape - best allround helper with long-lasting bonding power

The new tesa PRO Duct Tape 74613 will help you satisfy your customers. Due to its reliable bonding power and adaptability, your repair will be quick, clean and long-lasting. No matter whether you need to fixate cables during a painting job or seal a broken pipe, our PRO Duct Tape is suitable for most surfaces. The utility grade duct tape is based on synthetic rubber with a PET-fabric. The perfect addition for your craftsmen toolbox, easy to tear and always ready to go!

Features

- · Your best helper for all repairs and fixations: Quick to apply and easy to tear by hand, tesa PRO Duct Tape can be used both outdoors and indoors.
- · tesa PRO Duct Tape is water repellent and works even on slighlty rough surfaces. No matter the application, this tape fulfills the needs of every craftsmen.
- Due to its design, the tesa PRO Duct Tape is easy to unwind and adapts to every product to ensure clean sealing. Making your life easier, bond by bond!
- · This general purpose tape can be used for various applications such as repairing, marking, fastening, sealing and packaging.

Application

- This Duct Tape works best on clean, smooth surfaces
- · Apply the tape and press firmly onto the surface

Technical Information (average values)


The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

•	Backing material	PE-film with PET-	•	Tensile strength	40 N/cm
		filament	•	Temperature resistance max.	60 °C
•	Total thickness	175 μm	•	Mesh	27 count per square
•	Type of adhesive	synthetic rubber			inch
•	Elongation at break	13 %	•	Unwind force	3.5 N/cm

Adhesion to ctaal

• steel	8.0 N/cm •	rough surfaces	5.5 N/cm
Properties			
		T .	



Evaluation across relevant tesa® assortment: •••• very good ••• good •• medium • low



tesa® Professional 74613 PRO Duct Tape

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

