




**ELECTRICAL TEST:**  
 1.100% OPEN SHORT MIS WIRE TEST  
 2.CONTACT RESISTANCE:5 OHM MAX  
 3.INSULATION RESISTANCE:5M OHM MIN  
 4.HI-POT TEST:DC 300V/10ms  
 5.PASS 8K@60HZ TEST

CONSUMER ITEM	LENGTH (mm)
1M	1000±30
1.5M	1500±30



**PIN Assignment**



NO.	PART NAME	DESCRIPTION	QTY
⑥	CABLE	(1/0.254BC*1P+D1/0.254TCCS+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*4C+Filler+AL-Foil+144#/0.12AL BLACK PVC Jacket OD:6.3±0.15mm	m
⑤	SHELL	Black ABS SHELL	2PCS
④	MODEL	Black 45P PVC	g
③	Material	Tinplate	2PCS
②	MODEL	PE,Nature color	g
①	plug	DP M 20P PIN:G/F,SHELL: Gold plated	2PCS

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△	2021/07/09		A2
		YAN	YAN	FINISHING		△	2021/06/10		A1
				MATERIAL		SYM	DATE		REVISION