EXTERNAL DESKTOP POWER SUPPLY 12VDC 90WATT



POWERPAX: SW4333-B

Features:

- Universal Input
- IEC-320-C14 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,EN,FCC,GS,CE,RCM UL62368-1, EN62368-1, UKCA62368-1 (Pending)



Description:

Our Range of 90 Watt AC/DC switch mode power supplies provide 90 Watts of continuous output power in a high quality compact enclosure suitable for many general power applications.

Specification	
Part Number	SW4333-B
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C14
Input Current Rated	1.5A Max.
Inrush Current	≤60A at 110 Vac At cold start, maximum load
	≤120A at 220 Vac At cold start, maximum load
Efficiency	88% Min
Input Power (Output: No Load)	≤0.21W (CEC & DOE LEVEL VI Compliant)
Output Voltage Rating	12Vdc
Output Current Range	7.5A Max.
Output Min Current	0A
Output Connection Type	2.1 x 5.5 x 12 mm Centre Positive – Straight
Line and Load Regulation	+/-5%
Over Voltage Protection	V out 150% Max.
Over Current Protection	I out 170% Max.
Short Circuit Protection	Automatic recovery after short circuit fault being removed
Ripple Voltage	180mV
Hi-Pot	1800Vac 3mA 2sec.
Safety Approved	UL, CUL, EN, CB, CE, FCC, CCC, PSE, (UKCA pending)
EMI Standard	CISPR 32, EN 55032 Class B
Operating Temperature Range	0°C → +40°C
Storage Temperature	-20°C → +85°C
Operating Humidity	10% to 90%
Storage Humidity	5% to 90%
MTBF	30,000hrs
Dimensions	137(L) x 59(W) x 34(H) mm
Product Weight	450 g
Regulator Type	Switched Mode Power Supply

EXTERNAL DESKTOP POWER SUPPLY 12VDC 90WATT



POWERPAX: SW4333-B

Diagrams

