INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 6WATT



POWERPAX: SW4456-H

Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals



Description:

Our range of 6 Watt Interchangeable wall plug power supplies provide 6 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro, Auz & USA AC Heads, all Efficiency Level VI and carry worldwide safety approvals.


Specification	
Part Number	SW4456-H
Input Voltage Range	90-264 Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.18A max.
Input AC Heads	UK, Euro, Auz & USA
Output Voltage Rating	9V
Output Current Rated	0.67A
Output Min Current	0.01A
Output Connection Type	2.1x5.5x12mm centre positive – Straight
Total Output Regulation	+/-5%
Line and Load Regulation	+/-5%
Ripple & Noise	200mVp-p
Efficiency	79.03% min
Over Voltage Protection	auto restart
Over Load Protection	auto restart
Operating Temperature	0°C to 40°C
Storage Temperature	-20°C to +80°C
Operating Humidity	10% to 90%
Storage Humidity	10% to 90%
Hi-Pot	3000Vac 5mA 1min
Leakage Current	<0.25mA max
Safety Standard	CE, TUV, C-Tick, cUL
EMI Standard	EN55022:2006+A1:2007/ EN6100-3-2 / EN6100-3-3
MTBF	50K Hours
Size mm max.	55 x 45 x 36mm
Weight	160g

INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 6WATT



POWERPAX: SW4456-H

Diagrams



© TT Electronics plc