



As wires are individually inserted, the bundle is pre-formed. When harness is complete it can be easily snapped out. Three sizes available for 1/2" (12.7mm) 3/4" (19.0mm) and 1 1/4" (31.7mm) bundles.

Part Number:	RER1.25-S6-X
Product Family:	Elastic Retainers
Product Line:	Harness Board Accessories
RoHS Compliancy Status:	RoHS directive is not applicable
Part Description:	Harness Board Elastic Bundle Retainer
Product Type:	Harness Board Accessories
Material:	Nylon 6.6
Color:	Black Base, White Arm
Height (In.):	2.86
Height (mm):	72.6
Length (In.):	1.18
Length (mm):	30.0
Width (In.):	1.64

Width (mm):	41.7
Arm Color:	White
Arm Material:	Acetal
Base Color:	Black
Base Material:	Nylon
Environment:	Indoors
Hole Space (In.):	.83
Max. Bundle Diameter (In.):	1.25
Max. Bundle Diameter (mm):	31.8
Metric Screw Size:	M3
Mounting Method:	Two #6 (M3) Screws
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	10
Min. Order Qty.:	10