



- Speeds routing of wires
- Uniform driving depth is insured by a collar stop
- Smooth finish on nails prevents abrasion on wire jackets

Part Number: HBN1-T  
Product Family: Harness Board Nails  
Product Line: Harness Board Accessories

RoHS Compliancy Status: RoHS directive is not applicable

Part Description: Harness Board Nail

Material: Nickel Plated Steel

Diameter (In.): .075

Diameter (mm): 1.9

Length (In.): 1.00

Length (mm): 25.4

Environment: Indoors

Mounting Method: Hammered into Harness Board

Overall Length (In.): 1.62

Overall Length (mm): 41.1

Std. Pkg. UOM: PK

Thickness (In.): .073

Thickness (mm): 1.9

UOM: PC

Std. Pkg. Qty.: 200

Min. Order Qty.: 200