

Product data sheet

Specifications



XFMR DRY 3PH 112.5KVA 480V-208Y/120V

112T3HNV

Product availability : Stock - Normally stocked in distribution facility

Price* : 25,848.00 USD

Main

Product	Non-Ventilated Transformer
Enclosure Code	24E
Insulation Temperature	428 °F (220 °C)
Phase	3 phase
Primary Voltage	480 V delta
Power Rating	112.5 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	150 °C
Winding Material	Aluminium

Ordering and shipping details

Category	16273-NON VENT NON RESIN LVGP
Discount Schedule	PE2
GTIN	785901340270
Nbr. of units in pkg.	1
Package weight(Lbs)	1280.00 lb(US) (580.598 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	52.99 in (134.6 cm)
Package 1 width	29.49 in (74.9 cm)
Package 1 Length	35.98 in (91.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------