


# Product data sheet

Specifications



## TRANSFORMER DRY 3PH 6KVA 440V-220Y/127V

6T125F

Product availability : Stock - Normally stocked in distribution facility

Price\* : 2,892.00 USD

### Ordering and shipping details

|                       |                           |
|-----------------------|---------------------------|
| Category              | 16277-RESIN LVGP XFMR     |
| Discount Schedule     | PE2                       |
| GTIN                  | 785901464624              |
| Nbr. of units in pkg. | 1                         |
| Package weight(Lbs)   | 150.00 lb(US) (68.039 kg) |
| Returnability         | No                        |
| Country of origin     | MX                        |

### Packing Units

|                        |                      |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE                  |
| Package 1 Height       | 9.00 in (22.86 cm)   |
| Package 1 width        | 11.75 in (29.845 cm) |
| Package 1 Length       | 14.75 in (37.465 cm) |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| PVC free                   | Yes   |

\* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|