

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2140922030](#)  
**Status:** **Active**  
**Overview:** OneBlade 1.00mm-Pitch Wire-to-Board Connector System  
**Description:** OneBlade Receptacle Housing, 1.00mm Pitch, Single Row, Friction Lock, 3 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Product Specification 2140920000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2140929200-SPK-200 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">214092</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">OneBlade 1.00mm-Pitch Wire-to-Board Connector System</a>
Product Name	OneBlade
UPC	195842620667

**Physical**

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	49.920/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2140929200-SPK-200
Product Specification	2140920000-PS-000
Sales Drawing	2140920000-SD-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[214092](#) Series

**Mates With**

OneBlade Vertical Plug [214094](#) . OneBlade  
Right-Angle Plug [214097](#)

**Use With**

OneBlade Crimp Terminal [214093](#)