

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2180560205

Status:

Active

Overview:

EXTreme Guardian System

Description:

EXTreme Guardian Female-to-EXTreme Guardian Female Off-the-Shelf (OTS) Cable Assembly, 11.00mm Pitch, Single Row, 500.00mm Length, 2 Circuits, Black

Documents:

Drawing (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Assembly Configuration

Connector to Connector

Overview

Product Name

Type

UPC

Cable Assemblies

218056

Power, Wire-to-Board

Dual Ended Connectors

EXTreme Guardian Both Ends

EXTreme Guardian System

EXTreme Guardian

Discrete Wire Assembly

195842765986

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Single Ended

Termination Interface: Style

Wire Size AWG

Wire/Cable Type

500.00mm

2

Black

Female-Female

Yes

Copper Alloy

Gold

Tin

PBT

250.000/g

1

Bag

11.00mm

0.762µm

No

Crimp or Compression

6

UL 10669

Material Info

Reference - Drawing Numbers

Sales Drawing

2180560205-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)10043-DC (17

Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

218056 Series

Mates With

151035 EXTreme Guardian Power Right-Angle PCB Header, 151053 EXTreme Guardian Power Vertical PCB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION