

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2147192100](#)
Status: **Active**
Overview: [Zero-Hachi Connector System](#)
Description: Zero-Hachi Receptacle Housing, 0.80mm Pitch, Single Row, Friction Lock, 10 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2147190000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 2147199200-SPK-200 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	214719
Application	Signal, Wire-to-Board
Overview	Zero-Hachi Connector System
Product Name	Zero-Hachi
UPC	195842348417

Physical

Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Liquid Crystal Polymer
Net Weight	27.230/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2147199200-SPK-200
Product Specification	2147190000-PS-000
Sales Drawing	2147190000-SD-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214719 Series](#)

Mates With

Zero-Hachi Header [214721](#)

Use With

Zero-Hachi Crimp Terminal [214720](#)