

## Eaton NEMA 7/9 DC disconnect switch

**DS361UX**

**UPC:**782114858684

**Dimensions:**

- **Height:** 18.67 IN
- **Length:** 10.28 IN
- **Width:** 14.67 IN

**Weight:**89 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Single-throw
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 7/9
- **Enclosure Material:** Cast aluminum
- **Fuse Configuration:** Non-fusible
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Non-Fusible
- **Voltage Rating:** 600 Vac, 480 Vac, 250 Vdc
- **Design:** Complete unit
- **Max Hp Rating:** 5 at 250 Vdc, 15 at 480 Vac, 20 at 600 Vac
- **Wire Size:** #10-8 AWG Cu

**Supporting documents:**

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DS361UX](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data

