



- Clamp ties are used to attach a bundle to another surface such as a control panel wall or ceiling using another fastener.
- The design allows for bundling before or after screwing clamp in place.

Part Number: PLC1M-S4-C0
Product Family: *Pan-Ty*® Clamp Ties - Weather Resistant
Product Line: Clamp Cable Ties

RoHS Compliancy Status: Compliant

Part Description: Clamp Tie, 4.3", Miniature cross section

Product Type: Cable Ties

Material: Weather Resistant Nylon 6.6

Color: Black

CSA Certified: Yes

UL Listed (File #E56854): No

UL Recognized (File #E56854): Yes

Length (In.): 4.3

Length (mm): 109

Width (In.):	.100
Width (mm):	2.5
Boss Height (In.):	.153
Boss Height (mm):	3.9
Boss Width (In.):	.239
Boss Width (mm):	6.1
CE Compliant:	Yes
Cross Section:	Miniature
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	.75
Max. Bundle Diameter (mm):	19
Max. Continuous Use Temperature:	185°F (85°C)
Metric Screw Size:	M2.5
Min. Loop Tensile Strength (Lbs.):	18
Min. Loop Tensile Strength (N):	80
Nominal Hole Diameter (In.):	.122
Nominal Hole Diameter (mm):	3.1
Screw Size:	#4

Std. Pkg. UOM:	PK
Thickness (In.):	.045
Thickness (mm):	1.1
Tool:	GTS, GTSL, GS2B, PTS, PPTS, STS2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100