



- Wide tie body and high tensile strength are ideal for any application
- UV Black Weather Resistant Nylon 6.6 - can be used in outdoor applications
- Inline tie design allows parallel-entry of the tie into head resulting in a low profile on cable bundle
- Teeth on full length of body support a wider range of bundle diameters
- **IT Ties** – Outside teeth protect cable jacket and wire insulation
- **HV Ties** – Teeth on both sides of cable tie body provide additional surface for locking, enabling tie to conform to irregular bundle shapes while maintaining loop tensile strength

Part Number:	IT9100-C0
Product Family:	IN-LINE Cable Ties
Product Line:	IN-LINE Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	IN-LINE Cable Tie, 14.1", Light-Heavy cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	No
UL Listed (File #E56854):	No

UL Recognized (File #E56854):	No
Length (In.):	14.1
Length (mm):	358
Width (In.):	.350
Width (mm):	8.9
CE Compliant:	Yes
Cross Section:	Light-Heavy
Head Height (In.):	.300
Head Height (mm):	7.6
Head Width (In.):	.556
Head Width (mm):	14.1
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	3.94
Max. Bundle Diameter (mm):	100
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	124
Min. Loop Tensile Strength (N):	552
Std. Pkg. UOM:	PK

Thickness (In.):	.065
Thickness (mm):	1.7
Tool:	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100