



Specifications

Lamp Base Type	: E27
LED Colour	: Warm White
Dimmable	: Dimmable
Luminous Flux	: 560lm
Power Rating	: 7W
Voltage Rating	: 220V AC to 240V AC, 50/60Hz
Life Span	: 25000h
On/Off	: ≥15000
Temperature	: 3000K
CRI	: ≥80
Beam Angle	: 180°
Equivalent Power	: 45W
Efficiency Rating	: A+
Power/1000h	: 7kwh/1000h
Dimension(L × D)	: 108.5mm×60mm

Part Number Table

Description	Part Number
LED GLS Bulb, E27, Warm White, 3000K, Step Dimmable, 180°	PEL00246

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.