

Han F+B 17D SMC FI CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 517 3101
Specification	Han F+B 17D SMC FI CRT
HARTING eCatalogue	https://b2b.harting.com/09155173101

Identification

Category	Inserts
Series	Han [®] F+B

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	17
PE contact	Yes
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥3,000

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance

Material properties

Colour (insert) RAL 7032 (pebble grey)

Material flammability class acc. to UL 94 V-0

Commercial data

Packaging size 1

Net weight 15.87 g

Country of origin China

European customs tariff number 85389099

eCl@ss 27440205 Contact insert for industrial connectors