

Han F+B 5E SMC FI SCT 0,75 - 2,5 mm²




Image is for illustration purposes only. Please refer to product description.

Part number	09 15 505 2701
Specification	Han F+B 5E SMC FI SCT 0,75 - 2,5 mm ²
HARTING eCatalogue	https://b2b.harting.com/09155052701

Identification

Category	Inserts
Series	Han [®] F+B

Version

Termination method	Screw termination
Gender	Female
With wire protection	Yes
Number of contacts	5
PE contact	Yes

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm ²
Rated current	16 A
Rated voltage	600 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0

Commercial data

Packaging size	1
Net weight	25.6 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors