

Rotating Mirror Beacon 885 / Bulb

Halogen bulb GY6.35 12V 20W**Part No.:** 955.885.24**MECHANICAL DATA**

Height	44 mm
Diameter	10 mm
Weight with packaging	6 g
Product weight	3 g

ELECTRICAL DATA

Operating voltage	12V
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	12 VDC
Rated operational current	1667 mA
Power illuminant	20 W

OPTICAL DATA

Light source	halogen bulb
Lamp fitting/socket	GY6.35



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.