

Rotating Mirror Beacon 885 / Bulb  
**Halogen bulb GY6.35 24V 20W**



**Part No.:** 955.885.25

MECHANICAL DATA	
Height	42 mm
Diameter	10 mm
Weight with packaging	5 g
Product weight	2 g

ELECTRICAL DATA	
Operating voltage	24V
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	24 VDC
Rated operational current	833 mA
Power illuminant	20 W

OPTICAL DATA	
Light source	halogen bulb
Lamp fitting/socket	GY6.35

**!** For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.