

ROCKER SWITCHES

PRODUCT NUMBER 1807.1102



TECHNICAL DATA

Product number	1807.1102
Business unit	Switches, Sensors & Controls
Product Manager	-
Product family	Rocker switches
Packing unit	500
Miscellaneous	VDE
Weight	4.000 g
ROHS conform	yes
Output	catalog before 2009 / Web-Shop / catalog
Switching function	Lamp
connections	Quick-connect terminal, 4.8 x 0.8
Proof tracking	250 PTI
Insulation spacing	acc. to EN 61058 for reinforced or double insulation
Protection type	→ Connection IP 40 → Actuator IP 40
Ambient temperature	→ connection side -20 °C ... +85 °C
Ambient temperature	→ Actuation side min. -20 °C ... +55 °C
Storage temperature	-40 °C ... +80 °C
Housing description	housing: PA, black
Connection surface	→ bearing connection tinned → external connection tinned
Lighting	function illumination: window of PC, red function illumination: glow lamp, 230 V
Approval marks	VDE / CSA / UL
Suitable for appliances of protection class	II
Additional labeling	site, year, week of manuf. acc. to DIN EN 60062
Type of fastening	Snap fastening

Stock version



Technical changes reserved. Dimensions are not binding.
Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de