

720-6300 Series

Electronic LCD Hour Meter



The Model 720 Electronic Hour Meter offers a large 8 digit LCD display, (9999999.9) 0.32" (8mm) high, with an input operating voltage of 85-500VAC. The front of the unit is totally sealed, and the Hour Meter is housed in a rugged steel enclosure that is interchangeable with the Redington Model 720 Electro Mechanical Hour Meters. The wide operating voltage makes this product ideal for almost any application.

Key Features

- Operating voltage 85-500VAC
- Rugged steel housing
- Lithium battery
- Quartz accuracy (better than 0.01%)
- Popular 3-hole mounting

- Options include:
 - Gasket (721-0004)

Applications

- Test Equipment
- Control Panels
- Outdoor Lighting
- Compressors
- · Industrial Equipment





Specifications

Large 8 digit LCD (999999.9), 0.32" [8mm] high Display:

Reset: Non-reset

85-500VAC 50/60Hz Voltage:

Hour Meter Memory: Self-powered (internal lithium battery)

Wire leads 6" [152mm] **Termination:**

Panel (3-Hole) Mounting:

Temp. Range:

 -4° F to + 140°F(-20°C to +60°C) Operating: Storage: -40°F to +165°F (-40°C to +75°C)

Humidity: 0 to 95% RH, non-condensing, front totally sealed

Vibration: 10 to 80 Hz, 0.06 double amplitude


Shock: 50G

1000VAC 50/60Hz for 1 minute Dielectric:

Accuracy: Quartz accuracy (better than 0.01%)

Weight: 5.0 oz (142g)

Dimensions



Panel cutout: 2.16" [54.9] Dia. Mounting holes: 0.125" [3.2] Dia. on 2.44" [62.0] B.C.

Part Numbers

85-500VAC, non-reset, 3-hole round, 6" (152mm) wire leads 720-6300

Bury, BL9 9EF Tel: +44 161 674 0960 Email: sales.uk@trumeter.com Trumeter (The Americas) 6601 Lyons Rd, Suite H-7, Coconut Creek, Florida, FL 33073 USA

Tel: +1 954 725 6699 Email: sales.usa@trumeter.com Innovative Design Technologies Sdn. Bhd Lot 5881, Lorong lks Bukit Minyak 1

Taman Perindustrian Iks, 14000 Bukit Tengah Penang, Malaysia Web: www.idtworld.com

Tel: + 604 5015700 Email: sales.my@idtworld.com