

Rittal – The System.

Faster – better – everywhere.

► Compact enclosure AX Basic enclosure AX, sheet steel – AX 1350.000

Date : Apr 23, 2022

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Compact enclosure AX Basic enclosure AX, sheet steel – AX 1350.000

created: 23.04.2022 build on www.rittal.com/uk-en



Product description

Material:	Enclosure: Sheet steel Door: Sheet steel, all-round foamed-in PU seal
Surface finish:	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 1, 3R, 4, 12
Type rating to UL 50E:	Type 1, 3R, 4, 12
IK Code:	IK10
Supply includes:	Enclosure with door(s) Gland plate(s) in enclosure base Mounting plate Perforated door strip Lock: 3 mm double-bit
Basic material:	Sheet steel

Product description

Dimensions:	Width: 500 mm Height: 500 mm
--------------------	---------------------------------

Depth: 300 mm

Material thickness:	Enclosure: 1.5 mm Door: 1.5 mm Mounting plate: 2.5 mm
Mounting plate:	Width: 450 mm Height: 475 mm
Number of doors:	1
Door hinged on the right, may be swapped to the left:	yes
Number of cam locks:	2
Lock version:	Cam
Number of locks:	2
Lock insert:	3 mm double-bit
Gland plate, size:	6
Gland plate, qty.:	1
Packs of:	1 pc(s).
Weight/pack:	19 kg
EAN:	4028177813281
Customs tariff number:	94032080
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	AX Compact enclosure, WHD: 500x500x300 mm, sheet steel, with mounting plate, single-door, with two cam locks

Approvals

Approvals: Bureau Veritas

Certificates:	Certificate of manufacturer according to RMRS
----------------------	---

Declarations:	Declaration of conformity
----------------------	---------------------------
