LED Emergency Exit Signs





Features

RoHS Compliant

- Self-test option
- · Over-charge and Over-discharge protection
- · Custom-made Legend Panel
- · Wall mounted or Ceiling mounted
- SMD 2835 White LED 14 PCS
- Ni-Cd Battery 3.6V 900mAh
- 24 hours recharging time
- Robust steel housing
- Polycarbonate legend panel


Specifications

Voltage input : 220V AC to 240V AC 50Hz / 110V AC 60Hz

Charge Current : 80mA
Discharge Current : 270mA
Viewing Distance : 25m
LED Power : 0.9W

Dimensions (L×W×D) : 392mm×190mm×61mm

Diagram



Dimensions: Millimetres

Part Number Table

Description	Туре		Power Consumption	Weight	Part Number
LED Emergency Exit Sign	Maintained	Double Sides	3W	1.5kgs	PEL00783
	Non-Maintained		1.2W	1.4kgs	PEL00784
	Maintained	Single Side	3W	1.5kgs	PEL00781
	Non-Maintained		1.2W	1.4kgs	PEL00782

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

