INTERCHANGEABLE WALL PLUG POWER SUPPLY 5VDC 20WATT

Electronics

POWERPAX SW4127I

Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals
- Safety approved to: UL62368-1, EN62368-1, UKCA62368-1 (Pending)



Description:

Our range of 20 Watt Interchangeable wall plug power supplies provide 20 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro, USA & Auz AC Heads, all Efficiency Level VI and carry worldwide safety approvals.

Specification	
Part Number	SW4127I
Input Voltage Range	90-264 Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.58A Max
Input AC Heads	UK, Euro, USA & Auz
Output Voltage Rating	5V
Output Current Range	4A
Output Min Current	0A
Output Connection Type	2.1x5.5x12mm-Right angle
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	100mVp-p
Efficiency	75.18%Min
Over Voltage Protection	12V Max.
Over Load Protection	8A
Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to +80°C
Operating Humidity	10% to 90%
Storage Humidity	10% to 90%
Hi-Pot	3000Vac 10mA 1min
Leakage Current	0.25mA max
Safety Standard	UL,CUL,EN,PSE,BSMI,RCM,(UKCA pending)
EMI Standard	FCC/CE Class B
MTBF	30K Hours
Size mm max.	75 (L) x 35 (W) x 65 (H)
Weight	170g

INTERCHANGEABLE WALL PLUG POWER SUPPLY 5VDC 20WATT



POWERPAX SW4127I

Diagrams





