45 WATT CONSTANT VOLTAGE LED DRIVER



STONTRONICS: PAX1245TD-1

Features:

- Constant Voltage Output
- IP44 Rated
- Class II
- Compact Plastic Low Profile enclosure
- 2 Year Warranty



Description:

The Stontronics Range of 45 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP44 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications


Specification	
Part Number	PAX1245TD-1
Output Voltage Rating	12Vdc
Output Current	3A
Rated Power	45 Watt
Dimensions	170 x 50 x 31mm
Input Voltage Range	180-240VAC
Input Voltage Frequency	50-60Hz
Input Current	0.30A
Power Factor	>0.95
Efficiency	>80%
Short-circuit Protection	Auto-recovery
Over Current Protection	Auto-recovery
Over Voltage Protection	Auto-recovery
Operating Temperature	-30°C to +45°C
Storage Temperature	-40°C to +70°C
Relative Humidity	5% to 95%
Life Time	50K hours
EMI Standard	Meets Emissions to EN55022, EN55015 Class B
Safety Standard	Design refers to EN60598, EN61547, ENV5024, EN61000-4-2, 3, 4, 6, 8,11, EN61000-3-2, EN61000-3-3


45 WATT CONSTANT VOLTAGE LED DRIVER



STONTRONICS: PAX1245TD-1

Diagrams





© TT Electronics plc