EXTERNAL DESKTOP POWER SUPPLY 18VDC 65WATT

POWERPAX: SW4324-C

Features:

- Universal Input
- IEC-320-C14 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM





Description:

Our Range of 65 Watt AC/DC switch mode power supplies provide 65 Watts of continuous output power in a high quality compact enclosure suitable for many general power applications.


Specification	
Part Code	SW4324-C
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C14
Input Current	1.4A Max
Inrush Current	80 A Max. / 240 Vac (Cold start at 25°C, full load)
Leakage Current	<3.5mA
Efficiency	≥88%
Power Consumption	0.21 W (At 230Vac & No load)
Output Voltage Rating	18Vdc
Output Current Range	3.62A Max
Output Min Current	0A
Output Connection Type	2.1 x 5.5 x 12 mm centre positive – Straight
Line and Load Regulation	+/-5%
Over Voltage Protection	V out * 150% Max.
Over Current Protection	I out * 180% Max.
Short Circuit Protection	Automatic recovery after short-circuit fault being removed
Ripple Voltage	180mV Max.
Hi-Pot	3000Vac 10mA 1 min
Safety Approved	UL,CUL,GS,PSE,BSMI,CB,RCM
EMI Standard	CE / FCC Class B: Conduction & Radiation Met
Operating Temperature Range	0°C → +40°C
Storage Temperature	-20°C → +80°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Dimensions	115(L) x 53(W) x 38(H) mm
Product Weight	310g
Regulator Type	Switched Mode Power Supply

EXTERNAL DESKTOP POWER SUPPLY 18VDC 65WATT



POWERPAX: SW4324-C

Diagrams



POWERPAX