EXTERNAL DESKTOP POWER SUPPLY 5VDC 25WATT



POWERPAX: SW3125-C

Features:

- Universal Input
- IEC-320-C8 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM UL62368-1, EN62368-1, UKCA62368-1 (Pending)



Description:

Our Range of 25 watt AC/DC switch mode power supplies provide 25 watts of continuous output power in a high quality compact enclosure suitable for many general power applications.


Specification	
Part Code	SW3125-C
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C8
Input Current Rated	500mA Rms Max
Inrush Current	70A Max. / 230Vac
	Cold Start At 25°C Full Load
Leakage Current	0.25mA
Efficiency	85.02%
Input Power (Output: No Load)	<0.06W
Output Voltage Rating	4.96Vdc
Output Current Range	5A
Output Min Current	0A
Output Connection Type	2.1 x 5.5 x 12 mm centre positive – Straight
Over Voltage Protection	V out *180%(Max)
Over Load Protection	V out *180%(Max)
Short Circuit Protection	Automatic recovery after short-circuit fault being removed
Ripple Voltage	80 mV p-p Max.
Hi-Pot	3000Vac, 10mA, 1min.
Safety Approved	UL / CUL / EN / GS / PSE / BSMI / (UKCA pending)
EMI Standard	CE / FCC Class B
Operating Temperature Range	0°C → +40 °C
Storage Temperature	-20°C → +80°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Dimensions	(L) 99 x (W) 33 x (H) 50mm
Product Weight	170g
Regulator Type	Switched Mode Power Supply

EXTERNAL DESKTOP POWER SUPPLY 5VDC 25WATT



POWERPAX: SW3125-C

Diagrams



POWERPAX