

## Product information

# 13 82 200

## Pliers for Electrical Installation



### The all-rounder for professionals

- 6 functions in one pair of pliers
- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping wire ferrules
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the gripping surfaces for working on flush-mounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.75 - 1.5 mm<sup>2</sup> and 2.5 mm<sup>2</sup>
- Crimping die for wire ferrules 0.5 - 2.5 mm<sup>2</sup>
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm<sup>2</sup> / Ø 15 mm
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, multi stage oil-hardened



### General

Article No.	13 82 200
EAN	4003773075080
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	280 g
Dimensions	200 x 85 x 20 mm
Reach	no
RohS	no

### Technical details

Cutting capacity copper cable, multiple-stranded	Ø 15 mm
Cutting capacity copper cable, multiple-stranded	50 mm <sup>2</sup>
Stripping capacity for cross-sections	0.75 — 1.5 mm <sup>2</sup> / 2.5 mm <sup>2</sup>
Capacity in square millimetres	0.5 — 2.5 mm <sup>2</sup>
AWG	1 / 0

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27112148

technical change and errors excepted

