

Product information


35 21 115

Electronics Pliers

DIN ISO 9655



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Half-round jaws
- Ball bearing chrome steel, oil hardened




General

Article No.	35 21 115
EAN	4003773016724
Head	mirror polished
Handles	with non-slip plastic coating
Weight	55 g
Dimensions	115 x 68 x 11 mm
Standard	DIN ISO 9655
Reach	no
RohS	no

Technical details

Jaw length (B)	22.5 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	2.0 mm
Tips thickness (F)	1.5 mm
Head width (A)	11.0 mm



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

Spare Parts

35 99 01

Spare spring for electronics pliers, (2x)

technical change and errors excepted

