

Product information

44 10 J6

Circlip Pliers

For internal circlips in bore holes

- With locking device, can be released
- With replaceable tips made of tempered steel
- Black powder-coated
- DIN 5256 C, straight tips
- Pliers body: rolled steel, high-strength
- Tips: special tool steel, oil-hardened



General	
Article No.	44 10 J6
EAN	4003773024927
Pliers	black powder-coated
Weight	1,755 g
Dimensions	580 x 103 x 23 mm
Reach	yes
RohS	no

Technical details	
Size of bore	Ø 252 – 400 mm
Tips (diameter)	Ø 4.5 mm

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

Spare Parts	
44 19 J6	1 pair of spare tips for 44 10 J6,

technical change and errors excepted