

Product information

44 20 J61

Circlip Pliers

For internal circlips in bore holes

- With locking device, can be released
- With replaceable tips made of tempered steel
- Black powder-coated
- DIN 5256 D; 90° angled tips
- Pliers body: rolled steel, high-strength
- Tips: special tool steel, oil-hardened



∠90°

General	
Article No.	44 20 J61
EAN	4003773024965
Pliers	black powder-coated
Weight	1,723 g
Dimensions	600 x 142 x 19 mm
Reach	no
RohS	no
Technical details	
Size of bore	Ø 252 – 400 mm
Tips (diameter)	Ø 4.5 mm
Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140
Spare Parts	
44 29 J61	1 pair of spare tips for 44 20 J61,

technical change and errors excepted